

# Ball float mounting kit PVC for 1" electrochemical sensors

**Product #:** LZX914.99.42200  
**GBP Price:** Contact Us  
**Available**

Mounting hardware for easy installation of sensors on the basin rim (railing or wall). Pole with ball float and pivoting and swiveling bracket. Used on sites with variable water levels.

---

## Specifications

**Diameter:** Pipe: 48 mm

**Length:** 2300 mm immersion depth adjustable

**Material:** PVC

**Process connection:** 1 " NPT inner thread

**Process connection 2:** CPVC clamp and stainless steel mounting bracket for the installation on the railing (max. diameter 2") or concrete wall

**Special notes:** Composition:

Pole kit (2.3 m pipe, float, screw cap, etc.)

Pivoting and swiveling bracket (276G1200)

Sensor adapter (LZY276)